

## Product data sheet

### Characteristics

# INS51230

## OptiLine 50 - lid for 8 modules steel box - stainless steel

### Main

Product type	Lid
Cabling installation system	Floor outlet box
Type of floor	Hollow core floor In-cavity floor Raised floor
Floor box shape	Rectangular
Colour	Stainless steel
Quantity package 1 / unit	Set of 1

### Complementary

Suitable for	For 8 modules steel box
Fixing mode	Self-adhesive tape
Number of modules	8 modules
Product material	Die cast aluminium
Height	21 mm
Width	255 mm
Depth	278 mm

### Environment

IK degree of protection	IK07
IP degree of protection	IP20
Maximum load	10000 N

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	31.4 cm
Package 1 Length	33.4 cm
Package 1 Weight	1.5 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	330 mm
Package 2 Width	393 mm
Package 2 Length	393 mm
Package 2 Weight	10 kg

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>