

Product data sheet

Characteristics

INS51245

Floor Outlet Box Carcass, OptiLine 50, 8 modules



Main

Range	OptiLine
Product name	OptiLine 50
Device short name	OL50
Product type	Floor outlet box
Cabling installation system	Floor box
Type of floor	Raised floor In-cavity floor Hollow core floor
Floor box shape	Rectangular
Colour	Stainless steel

Complementary

Device presentation	Complete product
Device mounting	Floor mounted
Number of modules	8 modules
Product material	Stainless steel zinc coated
Height	88 mm
Width	235 mm
Depth	270 mm

Environment

IK degree of protection	IK07
IP degree of protection	IP20
Maximum load	10000 N

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.5 cm
Package 1 Width	32.8 cm
Package 1 Length	36.3 cm
Package 1 Weight	1.8 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations