

Product data sheet

Characteristics

INS62022

OptiLine 50, Socket outlet 16A, twin fascia
Horizontal for Australian standard, Red



Main

Range of product	OptiLine 50
Product type	Socket-outlet
Colour	Red (RAL 3003)
Outlet standard	Australian
Quantity package 1 / unit	Set of 5

Complementary

Number of socket	2
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	100 mm
Height	50 mm
Width	46.5 mm



Environment

Operating temperature	-5...40 °C
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.65 cm
Package 1 Width	4.96 cm
Package 1 Length	9.95 cm
Package 1 Weight	0.107 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
