

Product data sheet

Characteristics

INS62022

Socket outlet 16A - twin fascia Horizontal for Australian standard, Red



Main

Range of product	OptiLine 50
Product type	Socket-outlet
Colour	Red (RAL 3003)
Outlet standard	Australian
Quantity package 1 / unit	Set of 5

Complementary

Number of socket	2
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	100 mm
Height	50 mm
Width	46.5 mm






Environment

Operating temperature	-5...40 °C
IP degree of protection	IP20

Packing Units

Package 1 Weight	0.107 kg
Package 1 Height	46.500 mm
Package 1 width	49.600 mm
Package 1 Length	99.500 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile