

Product data sheet

Characteristics

INS62027

OptiLine, OptiLine 50 - VDI basic kit - flat -
1x30 Mech/Keystone - white



Main

Range	OptiLine
Product or component type	Central plate
Device application	Installation
Device presentation	Flat
CMS inst product add info	With dust cap
Colour tint	White (RAL 9010)
Quantity per set	Set of 1

Complementary

Device composition	Label Label window Mounting frame
Fixing mode	Snap-fitted: front opening
Socket number	1
Connector type	30-mech RJ45
Product compatibility	Mech Keystone
[Ue] rated operational voltage	250/400 V AC at 16 A
Material	PC/ABS
Length	30 mm
Height	50 mm
Width	50 mm

Environment

Ambient air temperature for operation	-5...40 °C
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	5 cm
Package 1 Length	5 cm
Package 1 Weight	22 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes