

## Product data sheet

### Characteristics

# INS62034

Floor box 12 module, complete, flush lid  
Stainless



### Main

Range	OptiLine
Product name	OptiLine 50
Device short name	OL50
Product type	Floor outlet box
Cabling installation system	Floor box
Type of floor	In-cavity floor Hollow core floor Raised floor
Floor box shape	Rectangular
Colour	Stainless steel
Quantity package 1 / unit	Set of 1

### Complementary

Number of modules	12 modules
Product material	Stainless steel zinc coated Die cast aluminium
Height	91 mm
Width	255 mm
Depth	378 mm

### Environment

Environmental health and issues	Halogen free
IK degree of protection	IK07
IP degree of protection	IP20

### Packing Units

Package 1 Weight	2.800 kg
Package 1 Height	215.000 mm
Package 1 width	328.000 mm
Package 1 Length	443.000 mm

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.