

Product data sheet

Characteristics

INS62034

OptiLine 50, 12 Module Fb and SS Flush Lid

Main

Range	OptiLine
Product name	OptiLine 50
Device short name	OL50
Product type	Floor outlet box
Cabling installation system	Floor box
Type of floor	In-cavity floor Hollow core floor Raised floor
Floor box shape	Rectangular
Colour	Stainless steel

Complementary

Device presentation	Complete product
Device mounting	Floor mounted
Number of modules	12 modules
Product material	Stainless steel zinc coated Die cast aluminium
Height	91 mm
Width	255 mm
Depth	378 mm


Environment

IK degree of protection	IK07
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.5 cm
Package 1 Width	32.8 cm
Package 1 Length	44.3 cm
Package 1 Weight	3.8 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations