

Product data sheet

Characteristics

INS62038

OptiLine 50, screeded floor box, 8 modules

Main

Range of product	OptiLine 50
Product or component type	Screeded floor box
Type of floor	Raised floor Hollow core floor In-cavity floor
Number of modules	8 modules
Quantity per set	Set of 1

Complementary

Material	Sheet steel zinc coated
Length	400 mm
Height	90 mm
Width	295 mm

Environment

IP degree of protection	IP20
IK degree of protection	IK07
Maximum load	10000 N

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20 cm
Package 1 Width	39 cm
Package 1 Length	44.5 cm
Package 1 Weight	5 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--