

Product data sheet

Characteristics

INS62038

Optiline 50 - screeded floor box - 8 modules



Main

Range of product	OptiLine 50
Product or component type	Screeded floor box
Type of floor	Raised floor Hollow core floor In-cavity floor
Number of modules	8 modules
Quantity per set	Set of 1

Complementary

Material	Sheet steel zinc coated
Length	400 mm
Height	90 mm
Width	295 mm

Environment

Environmental characteristic	Halogen free
IP degree of protection	IP20
IK degree of protection	IK07
Maximum load	10000 N

Packing Units

Package 1 Weight	4.000 kg
Package 1 Height	200.000 mm
Package 1 width	390.000 mm
Package 1 Length	445.000 mm

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.