

Product data sheet

Characteristics

INS68000

OptiLine 50 - junction box - white



Main

Range of product	OptiLine 50
Product type	Junction box
Provided equipment	Label window
Colour	White
Quantity package 1 / unit	1 piece

Complementary

Fixing mode	Snap-fitted
Product material	PC
Length	150 mm
Height	50 mm
Width	55 mm

Environment

Operating temperature	-5...40 °C
-----------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	102 g
Package 1 Height	6 cm
Package 1 width	7.2 cm
Package 1 Length	15.8 cm
Unit Type of Package 2	S03
Number of Units in Package 2	35
Package 2 Weight	4.1 kg
Package 2 Height	30 cm
Package 2 width	29.2 cm
Package 2 Length	38.8 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty

18 months
