

Product data sheet

Characteristics

ISM10554

OptiLine 45, stop end, PC/ABS, aluminium metallic



Main

Range of product	OptiLine 45 OptiLine 70
Cabling installation system	Trunking
Product type	Stop end
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 2

Complementary

Trunking material	Aluminium
Trunking dimension	185 x 55 mm
Fixing mode	Snap-fitted Screw
Product material	PC/ABS painted
Length	21 mm
Height	189 mm
Width	56 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP30
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.9 cm
Package 1 Width	5.6 cm
Package 1 Length	2.1 cm
Package 1 Weight	55.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------