

## Product data sheet

### Characteristics

# ISM10902

OptiLine 45, cable shelf, PVC (polyvinyl chloride), white



#### Main

Range of product	OptiLine 45 OptiLine 70
Cabling installation system	Trunking
Product type	Cable shelf
Colour	White (RAL 9010)
Quantity package 1 / unit	24 m

#### Complementary

Trunking material	Plastic Aluminium
Trunking dimension	75 x 55 mm 120 x 55 mm 165 x 55 mm 95 x 55 mm 155 x 55 mm 140 x 55 mm 185 x 55 mm 80 x 55 mm
Fixing mode	Snap-fitted
Product material	PVC (polyvinyl chloride)
Length	1000 mm
Height	17 mm
Width	47 mm

#### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP30

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.2 cm
Package 1 Width	4.7 cm
Package 1 Length	100.0 cm
Package 1 Weight	170.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	24

Package 2 Height	11.3 cm
Package 2 Width	15.0 cm
Package 2 Length	102.0 cm
Package 2 Weight	4.21 kg
Unit Type of Package 3	P12
Number of Units in Package 3	480
Package 3 Height	82.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	99.0 kg

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------