

Product data sheet

Characteristics

ISM10902

OptiLine 45 OptiLine 70 - cable shelf - PVC
(polyvinyl chloride) - white



Main

Range of product	OptiLine 45 OptiLine 70
Cabling installation system	Trunking
Product type	Cable shelf
Colour	White (RAL 9010)
Quantity package 1 / unit	24 m

Complementary

Trunking material	Plastic Aluminium
Trunking dimension	75 x 55 mm 120 x 55 mm 165 x 55 mm 95 x 55 mm 155 x 55 mm 140 x 55 mm 185 x 55 mm 80 x 55 mm
Fixing mode	Snap-fitted
Product material	PVC (polyvinyl chloride)
Length	1000 mm
Height	17 mm
Width	47 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP30

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty

18 months
