

Product data sheet

Characteristics

ISM10952

OptiLine 45, earthing device



Main

Cabling installation system	Service box Trunking Post Pole
Product or component type	Earthing device

Complementary

Type of pole	Two-sided One-sided
Type of post	Two-sided One-sided
Type of service box	Service box kit
Device presentation	Empty
Quantity per set	Set of 20
Trunking material	Aluminium
Trunking dimension	75 x 55 mm 155 x 55 mm 165 x 55 mm 185 x 55 mm 120 x 55 mm 140 x 55 mm 95 x 55 mm 80 x 55 mm
Product compatibility	Altira wiring device Unica wiring device
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted Free-standing
Material	Steel
Length	9 mm
Height	9 mm
Width	9 mm
Market segment	Residential Small commercial

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.890 cm
Package 1 Width	0.900 cm
Package 1 Length	0.900 cm
Package 1 Weight	1.100 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	1.000 cm
Package 2 Width	8.000 cm
Package 2 Length	12.000 cm
Package 2 Weight	25.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	240
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	506.000 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------