


Product data sheet

Characteristics

ISM10953

OptiLine 45 OptiLine 50 OptiLine 70 - earthing device - green yellow



Main

Cabling installation system	Trunking Post Service box Pole
Product or component type	Earthing device

Complementary

Type of pole	Two-sided One-sided
Type of post	Two-sided One-sided
Type of service box	Service box kit
Device presentation	Empty
Colour tint	Green Yellow
Quantity per set	Set of 10
Trunking material	Aluminium
Trunking dimension	155 x 55 mm 75 x 55 mm 120 x 55 mm 95 x 55 mm 165 x 55 mm 185 x 55 mm 140 x 55 mm 80 x 55 mm
Product compatibility	Altira wiring device Unica wiring device
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Free-standing Tension-mounted
Material	Aluminium
Length	200 mm
Market segment	Residential Small commercial

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-104
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	10 g
Package 1 Height	0.3 cm
Package 1 width	21.5 cm
Package 1 Length	8 cm
Unit Type of Package 2	S03
Number of Units in Package 2	500
Package 2 Weight	5.89 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------