

Product data sheet

Characteristics

ISM10955

OptiLine 45 OptiLine 70 - internal jointing and earthing piece - zinc



Main

Range of product	OptiLine 70 OptiLine 45
Cabling installation system	Trunking
Product type	Internal jointing and earthing piece
Quantity package 1 / unit	Set of 10

Complementary

Trunking material	Plastic Aluminium
Trunking dimension	140 x 55 mm 185 x 55 mm 80 x 55 mm 95 x 55 mm 155 x 55 mm 120 x 55 mm 165 x 55 mm 75 x 55 mm
Product material	Zinc untreated
Length	26 mm
Height	4 mm
Width	6 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	5 g
Package 1 Height	0.7 cm
Package 1 width	0.6 cm
Package 1 Length	2.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	51 g

Package 2 Height	0.7 cm
Package 2 width	7.5 cm
Package 2 Length	11.5 cm
Unit Type of Package 3	S02
Number of Units in Package 3	600
Package 3 Weight	3.515 kg
Package 3 Height	15 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------