

Product data sheet

Characteristics

ISM11100P

OptiLine 70 - installation trunking - 80x55 mm -
PVC - polar white - 2000 mm



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Polar white (RAL 9003)
Quantity per set	12 m

Complementary

Trunking material	Plastic
Trunking dimension	80 x 55 mm
Compartment partitioning	1 compartment
Mounting location	Internal
Fixing mode	By screws
Front opening size	70 mm
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	80 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Package 1 Weight	7.560 kg
Package 1 Height	12.000 cm
Package 1 width	25.500 cm
Package 1 Length	204.000 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile