

Product data sheet

Characteristics

ISM11100P

installation trunking, OptiLine 70, 80x55 mm,
PVC, polar white, 2000 mm



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Polar white (RAL 9003)
Quantity per set	12 m

Complementary

Trunking material	Plastic
Trunking dimension	80 x 55 mm
Compartment partitioning	1 compartment
Mounting location	Internal
Fixing mode	By screws
Front opening size	70 mm
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	80 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	8 cm
Package 1 Length	100 cm
Package 1 Weight	870 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	12.0 cm
Package 2 Width	25.5 cm

Package 2 Length	204.0 cm
Package 2 Weight	10.69 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	192
Package 3 Height	62.0 cm
Package 3 Width	120.0 cm
Package 3 Length	210.0 cm
Package 3 Weight	191.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations