

Product data sheet

Characteristics

ISM11104P

OptiLine 70 - stop end - 80 x 55 mm - PC/ABS
- polar white



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Stop end
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 2

Complementary

Trunking material	Plastic
Trunking dimension	80 x 55 mm
Fixing mode	Screw Snap-fitted
Product material	PC/ABS
Length	21 mm
Height	64 mm
Width	56 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	23 g
Package 1 Height	2.2 cm
Package 1 width	6 cm
Package 1 Length	8.5 cm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile