

## Product data sheet

### Characteristics

# ISM11107P

T-piece, OptiLine 70, 80 x 185 mm, PC/ABS, polar white



### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	T-piece
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

### Complementary

Trunking material	Plastic
Trunking dimension	120 x 55 mm 155 x 55 mm 80 x 55 mm 95 x 55 mm 185 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	102 mm
Height	52 mm
Width	57 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	5.7 cm
Package 1 Length	10.2 cm
Package 1 Weight	29 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations