

Product data sheet

Characteristics

ISM11151

OptiLine 70 - internal corner - PC/ABS - aluminium metallic



Main

| | |
|-----------------------------|--------------------|
| Range of product | OptiLine 70 |
| Cabling installation system | Trunking |
| Product type | Internal corner |
| Colour | Aluminium metallic |
| Quantity package 1 / unit | Set of 1 |

Complementary

| | |
|--------------------|----------------|
| Trunking material | Aluminium |
| Trunking dimension | 80 x 55 mm |
| Fixing mode | Snap-fitted |
| Product material | PC/ABS painted |
| Length | 117 mm |
| Height | 89 mm |
| Width | 117 mm |

Environment

| | |
|-------------------------|---|
| Standards | 73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102 |
| Operating temperature | -25...60 °C |
| IP degree of protection | IP40 |
| IK degree of protection | IK07 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 87 g |
| Package 1 Height | 8.9 cm |
| Package 1 width | 11.7 cm |
| Package 1 Length | 11.7 cm |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|