

Product data sheet

Characteristics

ISM11153

OptiLine 70, bend 90°, PC/ABS, aluminium metallic



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Bend 90°
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Aluminium
Trunking dimension	80 x 55 mm
Fixing mode	Snap-fitted Screw
Product material	PC/ABS painted
Length	107 mm
Height	107 mm
Width	57 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.7 cm
Package 1 Width	5.7 cm
Package 1 Length	10.7 cm
Package 1 Weight	92 g
Unit Type of Package 2	BAG
Number of Units in Package 2	30
Package 2 Height	30 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	3.451 kg

Unit Type of Package 3	PAL
Number of Units in Package 3	240
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	39.608 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------