

## Product data sheet

### Characteristics

# ISM11156

OptiLine 70, joint cover piece, PC/ABS, aluminium metallic



### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Joint cover piece
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

### Complementary

Trunking material	Aluminium
Trunking dimension	80 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS painted
Length	100 mm
Height	88 mm
Width	57 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.8 cm
Package 1 Width	5.7 cm
Package 1 Length	10 cm
Package 1 Weight	38 g
Unit Type of Package 2	BAG
Number of Units in Package 2	75
Package 2 Height	30 cm
Package 2 Width	29.9 cm
Package 2 Length	39.8 cm
Package 2 Weight	3.556 kg

Unit Type of Package 3	PAL
Number of Units in Package 3	600
Package 3 Height	45 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	40.448 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------