

Product data sheet

Characteristics

ISM11157

T-piece, OptiLine 70, PC/ABS, aluminium metallic

Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	T-piece
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Aluminium
Trunking dimension	185 x 55 mm 80 x 55 mm 95 x 55 mm 155 x 55 mm 120 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS painted
Length	102 mm
Height	52 mm
Width	57 mm

Environment


Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	5.7 cm
Package 1 Length	10.2 cm
Package 1 Weight	30.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	100
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm

Package 2 Length	40.0 cm
Package 2 Weight	3.71 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------