

Product data sheet

Characteristics

ISM11202P

OptiLine 70 - external corner - 95 x 55 mm -
PC/ABS - polar white



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	External corner
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Plastic
Trunking dimension	95 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	105 mm
Height	104 mm
Width	105 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	114 g
Package 1 Height	30 cm
Package 1 width	30 cm
Package 1 Length	40 cm
Unit Type of Package 2	S03
Number of Units in Package 2	20
Package 2 Weight	2.69 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile