

Product data sheet

Characteristics

ISM11203P

bend, OptiLine 70, 90°, 95 x 55 mm, PC/ABS,
polar white



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Bend 90°
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Plastic
Trunking dimension	95 x 55 mm
Fixing mode	Snap-fitted Screw
Product material	PC/ABS
Length	122 mm
Height	122 mm
Width	57 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.7 cm
Package 1 Width	12.2 cm
Package 1 Length	12.2 cm
Package 1 Weight	114 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations