

Product data sheet

Characteristics

ISM11206P

OptiLine 70 - joint cover piece - 95x 55 mm -
PC/ABS - polar white



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Joint cover piece
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1





Complementary

Trunking material	Plastic
Trunking dimension	95 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	100 mm
Height	100 mm
Width	57 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile