

Product data sheet

Characteristics

ISM11450

OptiLine 70, installation trunking, 155x55 mm, aluminium, natural, 2000 mm



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Natural
Quantity per set	4 m
Market segment	Residential Small commercial

Complementary

Trunking material	Aluminium
Trunking dimension	155 x 55 mm
Compartment partitioning	2 compartments
Mounting location	Internal
Fixing mode	By screws
Front opening size	70 mm
Material	Aluminium anodized
Length	2000 mm
Height	155 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	165 cm
Package 1 Width	225 cm
Package 1 Length	2000 cm
Package 1 Weight	9.8 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------