

Product data sheet

Characteristics

ISM11454

OptiLine 70, stop end, PC/ABS, aluminium metallic



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Stop end
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 2

Complementary

Trunking material	Aluminium
Trunking dimension	155 x 55 mm
Fixing mode	Snap-fitted Screw
Product material	PC/ABS painted
Length	21 mm
Height	159 mm
Width	56 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.9 cm
Package 1 Width	5.6 cm
Package 1 Length	2.1 cm
Package 1 Weight	35 g
Unit Type of Package 2	BAG
Number of Units in Package 2	2
Package 2 Height	3 cm
Package 2 Width	6 cm
Package 2 Length	17.5 cm
Package 2 Weight	94 g

Unit Type of Package 3	S03
Number of Units in Package 3	150
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	7.607 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------