

Product data sheet

Characteristics

ISM11456

OptiLine 70, joint cover piece, PC/ABS, aluminium metallic



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Joint cover piece
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Aluminium
Trunking dimension	155 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS painted
Length	100 mm
Height	160 mm
Width	57 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------