

Product data sheet

Characteristics

ISM11500P

installation trunking, OptiLine 70, 185x55 mm,
PVC, polar white, 2000 mm



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Polar white (RAL 9003)
Quantity per set	8 m

Complementary

Trunking material	Plastic
Trunking dimension	185 x 55 mm
Compartment partitioning	2 compartments
Fixing mode	By screws
Front opening size	70 mm
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	185 mm
Width	55 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	5.5 cm
Package 1 Width	18.5 cm
Package 1 Length	200 cm
Package 1 Weight	3.97 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	12 cm
Package 2 Width	8 cm
Package 2 Length	204 cm

Package 2 Weight	16.37 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	128
Package 3 Height	62 cm
Package 3 Width	120 cm
Package 3 Length	210 cm
Package 3 Weight	282 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations