

## Product data sheet

### Characteristics

# ISM11501P

OptiLine 70 - internal corner - 185 x 55 mm -  
PC/ABS - polar white



#### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Internal corner
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

#### Complementary

Trunking material	Plastic
Trunking dimension	185 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	117 mm
Height	194 mm
Width	117 mm

#### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	137 g
Package 1 Height	12 cm
Package 1 width	17 cm
Package 1 Length	19 cm
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Weight	1.78 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>