

## Product data sheet

### Characteristics

# ISM11502P

OptiLine 70, external corner, 185 x 55 mm, PC/  
ABS, polar white



#### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	External corner
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

#### Complementary

Trunking material	Plastic
Trunking dimension	185 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	105 mm
Height	194 mm
Width	105 mm

#### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	13.5 cm
Package 1 Length	19.5 cm
Package 1 Weight	161 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>