

## Product data sheet

### Characteristics

# ISM11505P

wall/ceiling frame, OptiLine 70, 185 x 55 mm,  
PC/ABS, polar white



#### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Wall/ceiling frame
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

#### Complementary

Trunking material	Plastic
Trunking dimension	185 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	22 mm
Height	240 mm
Width	82 mm

#### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	8.5 cm
Package 1 Length	24 cm
Package 1 Weight	48 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations