

## Product data sheet

### Characteristics

# ISM11550

installation trunking, OptiLine 70, 185x55 mm,  
aluminium, natural, 2000 mm

### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product or component type	Installation trunking
Colour tint	Natural
Quantity per set	4 m
Market segment	Residential Small commercial

### Complementary

Trunking material	Aluminium
Trunking dimension	185 x 55 mm
Compartment partitioning	2 compartments
Mounting location	Internal
Fixing mode	By screws
Front opening size	70 mm
Material	Aluminium anodized
Length	2000 mm
Height	185 mm
Width	55 mm

### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Height	195 cm
Package 1 Width	225 cm
Package 1 Length	2000 cm
Package 1 Weight	12 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	4
Package 2 Height	19.5 cm
Package 2 Width	22.5 cm
Package 2 Length	206 cm
Package 2 Weight	24 kg

Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	72.5 cm
Package 3 Width	120 cm
Package 3 Length	205 cm
Package 3 Weight	375.76 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------