

## Product data sheet

### Characteristics

# ISM11551

OptiLine 70, internal corner, PC/ABS,  
aluminium metallic



#### Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Internal corner
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

#### Complementary

Trunking material	Aluminium
Trunking dimension	185 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS painted
Length	117 mm
Height	194 mm
Width	117 mm

#### Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.7 cm
Package 1 Width	11.7 cm
Package 1 Length	19.4 cm
Package 1 Weight	125.1 g
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.96 kg

Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	26.968 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------