

Product data sheet

Characteristics

ISM11553

OptiLine 70 - bend 90° - PC/ABS - aluminium metallic



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Bend 90°
Colour	Aluminium metallic
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Aluminium
Trunking dimension	185 x 55 mm
Fixing mode	Screw Snap-fitted
Product material	PC/ABS painted
Length	212 mm
Height	212 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	234 g
Package 1 Height	5.7 cm
Package 1 width	21.2 cm
Package 1 Length	21.2 cm
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Weight	3.05 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12

Number of Units in Package 3	80
Package 3 Weight	35.61 kg
Package 3 Height	45 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------