

Product data sheet

Characteristics

ISM11900P

OptiLine 70 - front cover - 70 mm - PVC - polar white



Main

Range of product	OptiLine 70
Cabling installation system	Trunking
Product type	Front cover
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	24 m

Complementary

Trunking material	Plastic
Trunking dimension	120 x 55 mm 185 x 55 mm 80 x 55 mm 155 x 55 mm 95 x 55 mm
Fixing mode	Snap-fitted
Product material	PVC (polyvinyl chloride)
Length	2000 mm
Height	71 mm
Width	13 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1 NF C 68-102
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Weight	430.0 g
Package 1 Height	0.1 cm
Package 1 width	7 cm
Package 1 Length	200 cm
Unit Type of Package 2	PAL
Number of Units in Package 2	1512
Package 2 Weight	377.0 kg

Package 2 Height	68 cm
Package 2 width	120 cm
Package 2 Length	210 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	24
Package 3 Weight	5.66 kg
Package 3 Height	6 cm
Package 3 width	12 cm
Package 3 Length	204 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile