

Product data sheet

Characteristics

ISM11901

OptiLine 70 - cable retainer - blue



Main

Cabling installation system	Trunking
Product or component type	Cable retainer

Complementary

Colour tint	Blue (NCS S 3050-R90B)
Quantity per set	Set of 5
Trunking material	Aluminium Plastic
Trunking dimension	120 x 55 mm 185 x 55 mm 155 x 55 mm 95 x 55 mm 80 x 55 mm
Fixing mode	Snap-fitted
Material	PA (polyamide)
Length	25 mm
Height	42 mm
Width	48 mm
Market segment	Small commercial Residential

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

Packing Units

Package 1 Weight	3.100 g
Package 1 Height	25.000 mm
Package 1 width	25.000 mm
Package 1 Length	41.000 mm

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------