


Product data sheet

Characteristics

ISM11950

OptiLine 70 - front cover - natural



Main

Cabling installation system	Post Trunking Pole
Product or component type	Front cover

Complementary

Type of pole	Two-sided One-sided
Type of post	Two-sided One-sided
Colour tint	Natural
Quantity per set	24 m
Trunking material	Aluminium
Trunking dimension	120 x 55 mm 185 x 55 mm 80 x 55 mm 155 x 55 mm 95 x 55 mm
Pole/post surface finish	Anodized
Pole fixing mode	Free-standing Tension-mounted
Fixing mode	Snap-fitted
Material	Aluminium anodized
Length	2000 mm
Height	71 mm
Width	13 mm
Market segment	Small commercial Residential

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	2
Package 1 Weight	678 g
Package 1 Height	71 mm
Package 1 width	13 mm
Package 1 Length	2000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------