

Product data sheet

Characteristics

ISM20505

OptiLine, OptiLine 70 - pole - tension-mounted
- two-sided - natural - 3170-3570 mm



Main

Range	OptiLine
Product name	OptiLine 70
Cabling installation system	Pole
Product type	Pole
Type of pole	Two-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	3170...3570 mm
Depth	118 mm
Width	120 mm

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	15.000 cm
Package 1 Width	28.000 cm
Package 1 Length	325.000 cm
Package 1 Weight	16.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	20
Package 2 Height	93.000 cm
Package 2 Width	120.000 cm
Package 2 Length	340.000 cm
Package 2 Weight	330.000 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------