

Product data sheet

Characteristics

ISM20507

OptiLine 70 - pole - tension-mounted - two-sided - natural - 5170-5570 mm



Main

Range	OptiLine
Product name	OptiLine 70
Cabling installation system	Pole
Product type	Pole
Type of pole	Two-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	5170...5570 mm
Depth	118 mm
Width	120 mm
Market segment	Small commercial Residential

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Package 1 Weight	12.500 kg
------------------	-----------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------