

Product data sheet

Characteristics

ISM20508

OptiLine 70 - pole - tension-mounted - two-sided - natural - 6170-6570 mm



Main

Range	OptiLine
Product name	OptiLine 70
Cabling installation system	Pole
Product type	Pole
Type of pole	Two-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	6170...6570 mm
Depth	118 mm
Width	120 mm
Market segment	Residential Small commercial

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11.5 kg
Package 1 Height	10 cm
Package 1 width	12 cm
Package 1 Length	10 cm

Contractual warranty

Warranty	18 months
----------	-----------