

Product data sheet

Characteristics

ISM20508

Pole, OptiLine 70, tension-mounted, two-sided, natural, 6170-6570 mm

Main

Range	OptiLine
Product name	OptiLine 70
Cabling installation system	Pole
Product type	Pole
Type of pole	Two-sided
Pole/post surface finish	Anodized
Pole fixing mode	Tension-mounted

Complementary

Additional information	Adjustability of ceiling fixing 400 mm
Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	6170...6570 mm
Depth	118 mm
Width	120 mm

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	12.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	11.5 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	28
Package 2 Height	64.9 cm
Package 2 Width	120.0 cm
Package 2 Length	256.0 cm
Package 2 Weight	356.944 kg

Contractual warranty

Warranty	18 months
----------	-----------
