

Product data sheet

Characteristics

ISM20520

OptiLine, OptiLine 70 - pole - free-standing - one-sided - natural - 2385 mm



Main

Range	OptiLine
Product name	OptiLine 70
Shape	Oval
Cabling installation system	Pole
Product type	Pole
Device presentation	Empty
Type of pole	One-sided
Pole/post surface finish	Anodized
Pole fixing mode	Free-standing
Adjustment	Fixed: 0 mm

Complementary

Colour	Natural
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	2385 mm
Depth	120 mm
Width	61 mm
Cover type	2 closed cover cover 70 mm in aluminium anodized
Useful cross section	4256 mm ²
Compartment partitioning	1 compartment

Environment

Standards	73/23/EEC 93/68/EEC IEC 1084-2-4 SS 424 10 32 EN-AW-6063
Operating temperature	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.1 cm
Package 1 Width	12.0 cm
Package 1 Length	238.5 cm
Package 1 Weight	6.15 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	28
Package 2 Height	64.9 cm
Package 2 Width	255.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	207.116 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------