

## Product data sheet

### Characteristics

# ISM20553

## OptiLine 70, ceiling fixing, white



### Main

Cabling installation system	Pole
Product or component type	Ceiling fixing

### Complementary

Type of pole	Two-sided One-sided
Colour tint	White (RAL 9010)
Quantity per set	Set of 1
Pole/post surface finish	Powder coated Anodized
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	Steel powder coated
Length	126 mm
Height	75 mm
Width	72 mm
Market segment	Small commercial Residential

### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	7.5 cm
Package 1 Length	12.6 cm
Package 1 Weight	393 g
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	39.8 cm
Package 2 Width	30 cm
Package 2 Length	29.9 cm
Package 2 Weight	10.665 kg
Unit Type of Package 3	PAL

Number of Units in Package 3	200
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	105.32 kg

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------