

## Product data sheet

### Characteristics

# ISM20554

## ceiling fixing, OptiLine 70, white

### Main

Cabling installation system	Pole
Product or component type	Ceiling fixing

### Complementary

Type of pole	One installation box Two installation boxes
Colour tint	White (RAL 9010)
Quantity per set	Set of 1
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Tension-mounted
Fixing mode	By screws
Material	Steel powder coated
Height	75 mm
Diameter	72 mm
Market segment	Small commercial Residential

### Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.2 cm
Package 1 Length	7.2 cm
Package 1 Weight	290 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	39.8 cm
Package 2 Width	30 cm
Package 2 Length	29.9 cm
Package 2 Weight	15.39 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	400

Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	143.12 kg

### Contractual warranty

Warranty	18 months
----------	-----------