

Product data sheet

Characteristics

ISM20555

OptiLine 70, partition profile, white



Main

Cabling installation system	Pole
Product or component type	Partition profile

Complementary

Type of pole	One-sided Two-sided
Colour tint	White (RAL 9010)
Quantity per set	Set of 10
Pole/post surface finish	Anodized Powder coated
Pole fixing mode	Free-standing Tension-mounted
Fixing mode	Snap-fitted
Material	ABS (acrylonitrile butadiene-styrene)
Length	50 mm
Height	500 mm
Width	49 mm
Market segment	Small commercial Residential

Environment

Ambient air temperature for operation	-25...60 °C
IP degree of protection	IP40

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	50.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	96.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	13.0 cm
Package 2 Width	15.5 cm
Package 2 Length	102.5 cm
Package 2 Weight	1.368 kg

Unit Type of Package 3	PAL
Number of Units in Package 3	300
Package 3 Height	90.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	67.04 kg

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------