

Product data sheet

Characteristics

ISM20555

OptiLine 70 - partition profile - white



Main

| | |
|-----------------------------|-------------------|
| Cabling installation system | Pole |
| Product or component type | Partition profile |

Complementary

| | |
|--------------------------|---------------------------------------|
| Type of pole | One-sided Two-sided |
| Colour tint | White (RAL 9010) |
| Quantity per set | Set of 10 |
| Pole/post surface finish | Anodized Powder coated |
| Pole fixing mode | Free-standing Tension-mounted |
| Fixing mode | Snap-fitted |
| Material | ABS (acrylonitrile butadiene-styrene) |
| Length | 50 mm |
| Height | 500 mm |
| Width | 49 mm |
| Market segment | Small commercial Residential |

Environment

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -25...60 °C |
| IP degree of protection | IP40 |

Packing Units

| | |
|------------------|------|
| Package 1 Weight | 96 g |
|------------------|------|

Offer Sustainability

| | |
|----------------------------|--|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| Environmental Disclosure |  Product Environmental Profile |

Contractual warranty

Warranty

18 months
