

## Product data sheet

### Characteristics

# ISM20600

OptiLine 70, post, one-sided, natural, 333 mm



### Main

Range of product	OptiLine 70
Cabling installation system	Post
Product type	Post
Type of post	One-sided
Pole/post surface finish	Anodized

### Complementary

Colour	Natural
Fixing mode	Screw-fixed
Front opening size	70 mm
Material	Aluminium anodized
Quantity package 1 / unit	Set of 1
Height	333 mm
Width	100 mm
Market segment	Residential Small commercial

### Environment

Standards	73/23/EEC 93/68/EEC EN-AW-6063 IEC 1084-2-4 SS 424 10 32
Operating temperature	-25...60 °C
IP degree of protection	IP40

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	10.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	830.0 g

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------